

A Donaldson Company

A WORLD LEADER IN FUME EXTRACTION TECHNOLOGY

AD Oracle SA iQ

Last Updated on 08.04.2021





The complete, compact, global solution for high performance laser fume extraction system.

Introducing BOFA's most technically advanced compact laser fume extractor. The AD Oracle SA iQ has been enhanced with BOFA's iQ Operating System, RFA and ACF technology and packs a powerful range of unique features into one compact unit.

The iQ Operating System performs at two distinct levels: Operators benefit from the ease of operation and clarity of real time information and the system provides a cache of analytical data, enabling users to download performance and operating parameters for evaluation purposes.

The iQ system takes performance and safety parameters to a new level and ensures that maintenance downtime and ownership costs are kept to a minimum.

More information about the Intelligent Operating System (iQ).

Technology



Intelligent Operating System (iQ)



HEPA filter



Automatic flow control (AFC) technology



Reverse flow air (RFA) technology



Advanced carbon filter (ACF) technology



Multi voltage sensing (MVS) unit



Patented technology



ProTECT service plan



SureCHECK quality standard

Key features of the AD Oracle SA iQ

iQ Operating System Standard

Reverse flow air filter technology (RFA)

Auto sensing voltage (90v - 257v) - For global use Standard

Automatic flow control

Standard

Advanced carbon filter technology (ACF)

Standard

High contrast display

Standard

Contact BOFA at https://bofainternational.com/en/contact/

https://bofainternational.com/en/portal/datasheets/ad-oracle-sa-iq/















Real time airflow reading

Standard

'Run safe' operation

Standard

Low cost replacement filters

Standard

Low noise levels

Standard

Small footprint

Standard

Interfacing with host laser

Optional

Filter change / system fail signal

Optional

Independent filter condition monitoring

Standard

Remote diagnostics via USB

Standard

HEPA and gas combined filter

Standard

Lockable castors

Standard

VOC gas sensor (Volatile Organic Compound)

Optional

Remote stop / start interface

Optional

Optional filter medias

. Optional

Technical specification

1. iQ display

5. Door latches

9. Door hinges

2. On / off switch

6. Hose inlet connection -

75mm

10. Standby button

3. Power cable7. Exhaust outlet

4. Signal / interface cable

8. Motor cooling inlet



Airflow through filters

Chemical filter



HEPA filter



Pre-filter




Clean air



Contaminated air



Particulate



Technical data		
	EU	US
Dimensions (HxWxD)	745 x 450 x 515 mm	29.33 x 17.72 x 20.28"
Cabinet construction	Brushed stainless steel / Powder coated mild steel	Brushed stainless steel / Powder coated mild steel
Airflow / Pressure	380m³/hr / 96mbar	223cfm / 96mbar
Electrical data	90 - 257v Single-phase 1~ 50/60Hz Full load current: 12.5 amps / 1.1kw	90 - 257v Single-phase 1~ 50/60Hz Full load current: 12.5 amps / 1.1kw
Noise level	< 60dBA (at typical operating speed)	< 60dBA (at typical operating speed)
Weight	58kg	128lbs
Approvals	UKCA and CE	cUL, UL*

Pre-filter specifications		
Surface media area	3.15m² approx (33.894 ft²)	
Filter media	Borosilicate	
Filter media construction	Folded pleat	
Filter housing	Cardboard	
Filter efficiency	95% @ 0.9 microns	

Combined filter specifications		
HEPA filter media	Borosilicate	
HEPA media construction	Maxi pleat construction with glue bead spacers	
Filter housing	Zintec mild steel	
Treated activated carbon	15kgs (33 lbs)	
Filter efficiency	99.997% @ 0.3 microns	

Part numbers						
Model	Voltage	Part no.	24V stop / start	Filter change / system failure signal	VOC monitoring	Hose kit
AD Oracle SA iQ stainless steel	90V - 257V	L2374	A2001	A2002	A2003	A1020008
AD Oracle SA iQ powder coated	90V - 257V	L2364	A2001	A2002	A2003	A1020008

Replacement filters			
Model	Pre-filter	Combined filter	
AD Oracle SA iQ	A1030344	A1030155	

^{*} Tested to UL and cUL standards, but testing may be provided by alternate nationally recognised test laboratories. Certain product configurations may affect the UL certification. Please speak to your sales representative.

Other languages

AD Oracle SA iQ French

Datasheet correct at time of publishing.

Where applicable, the carbon used in BOFA units is capable of removing a wide range of VOC's, however it is the responsibility of the user to ensure the carbon is suitable for their application. For specific applications, please contact us for details.

Think before you print! Please consider the environment before printing this document.

